

Basic Data

Suitable for

Mounting in boards. Suitable even for ceiling mounting due to large captive toggle.

Applications

For installation in 10 to 35 mm plasterboards.

Advantages

- Fireproof
- Captive fixing – even without screw
- High load values
- Wide range of board thicknesses
- No tool required
- Large metal toggle, withstands humidity, heat and heavy loads
- Simple to remove – cut off spring
- Two variants – with screw or hook

Material

Toggle and collar – zinc




Screw and hook – electroplated steel

Spring – steel


Packaging

Cardboard carton.


Dimensions of hook for TPP-10xM4K:



Drill a hole in accordance with the table. Attach the toggle in the guide collar and install.



Push screw until spring-loaded bar flips over.



Remove the screw. Mount the fixture.

Range	Type	Colour	Qty/Pack	Art. No.
Cavity fixing with screw				
P80837		TPP-10xM4S	–	1200 005 EA947BB-4
		TPP-13xM5S	–	1200 401 EA947BB-5
Cavity fixing with hook				
P80837		–	25	1200 203 EA947BA-4

Technical data (1 kN = 100 kg)							
Type Ø mm × thread	Screw size	Drill Ø mm	Sheet thickness mm	Max thickness of fixture for sheet thickness		Practical loading capacity Shear/pull-out ¹⁾ kN	
				13 mm	2x13 mm	13 mm plaster- board	2x13 mm plaster- board
TPP-10xM4S	M4x55	10	10–30	37 mm	24 mm	0.40/0.16	0.60/0.22
TPP-10xM4K	M4x50	10	10–26	–	–	– /0.16	– /0.22
TPP-13xM5S	M5x65	13	10–35	47 mm	34 mm	0.50/0.17	0.80/0.34

¹⁾ Includes a safety factor of 2.5 for shear and 3 for pull-out.