

EA986GA-125



EAN: 4047526042622

ID: 42622

Pressed steel fixed castor, medium duty brackets, with top plate fitting, Wheels with 'Blickle Comfort' two-component solid rubber tyres, with pressed steel rim


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of 'Blickle Comfort' two-component solid rubber, with hard rubber core and highly elastic rubber tread, very high operational comfort, low-noise operation, compared to standard solid rubber the operational comfort and the load capacity are increased whereas the rolling resistance is reduced, very good floor preservation. Tread colour: black

Rim / wheel centre: Pressed steel rim with tubular steel hub, pressed rim (special shock and impact-resistant design), zinc-plated, blue-passivated, Cr6-free. Tyre pressed with rim.



Technical data

| | |
|-------------------------|-------------|
| Wheel Ø (D) | 125 mm |
| Wheel width (T2) | 37,5 mm |
| Load capacity | 120 kg |
| Total height (H) | 150 mm |
| Unit weight | 1.05 kg |
| Temperature range from | -25 °C |
| Temperature range to | 80 °C |
| Tread & tyre hardness | 65° Shore A |
| Bearing type | |
| Plate size (A,B) | 100 x 85 mm |
| Bolt hole Ø (d) | 9 mm |
| Bolt hole spacing (a,b) | 80 x 60 mm |

Rolling resistance





Operating noise



Floor surface preservation



B-RD 125R

| Variants | |
|---|--|
|  | With pressed steel thread guard, zinc-plated |
|  | With non-marking grey tyre, 56° shore A |