






軸用C形止め輪《STW-3~56》

適用する軸



サイズNo.	溝底r(最大)
7未満	鋭角
7~10未満	0.08
10~26未満	0.13
26以上	0.25

d4は止め輪をd1にはめる時の外周の最大径
(クリアランス外径)

サイズNo.9以下 サイズNo.170以上

単位：mm

サイズNo.	止 め 輪							適 用 す る 軸						
	d3		t		b	a	d0	d4 (参考)	d1	d2		m		参考 n
	基本寸法	公 差	基本寸法	公 差	約	約	最小			基本寸法	公 差	基本寸法	公 差	
STW- ※ 3	2.7	+0.04	0.25	±0.025	0.5	1.7	0.7	7	3	2.85		0.35		0.3
EA949DA-104 ※ 4	3.7	-0.15	0.4	±0.03	0.9	2.2	0.8	9	4	3.8	0	0.5		0.3
EA949DA-105 ※ 5	4.7		0.6		1.1	2.4	0.8	10.5	5	4.8	-0.04	0.7	+0.1	0.3
EA949DA-106 ※ 6	5.6		0.7	±0.04	1.3	2.8	1	12	6	5.7		0.8	0	0.5
EA949DA-107 ※ 7	6.5	+0.06	0.8		1.4	3	1	14	7	6.7	0	0.9		0.5
EA949DA-108 ※ 8	7.4	-0.2	0.8		1.6	3	1	15	8	7.6	-0.06	0.9		0.6
EA949DA-109 ※ 9	8.4		1		1.8	3.2	1	16	9	8.6		1.15		0.6
EA949DA-110 ※ 10	9.3	±0.15	1		1.8	3	1.2	17	10	9.6	0.09	1.15		1.5
EA949DA-111 ※ 11	10.2		1		2	3.1	1.2	18	11	10.5		1.15		1.5
EA949DA-112 ※ 12	11.1		1		2.1	3.2	1.5	19	12	11.5		1.15		1.5
EA949DA-113 ※ 13	12		1	±0.05	2.1	3.3	1.5	20	13	12.4		1.15		1.5
EA949DA-114 ※ 14	12.9		1		2.2	3.4	1.7	22	14	13.4	0	1.15		1.5
EA949DA-115 ※ 15	13.8	±0.18	1		2.2	3.5	1.7	23	15	14.3	-0.11	1.15		1.5
EA949DA-116	14.7		1		2.2	3.6	1.7	24	16	15.2		1.15		1.5
EA949DA-117	15.7		1		2.2	3.7	1.7	25	17	16.2		1.15		1.5
EA949DA-118	16.5		1.2		2.6	3.8	1.7	26	18	17		1.35		1.5
EA949DA-119	17.5		1.2		2.7	3.8	2	27	19	18		1.35		1.5
EA949DA-120	18.5		1.2		2.7	3.9	2	28	20	19		1.35		1.5
EA949DA-121	19.5		1.2		2.7	4	2	30	21	20		1.35		1.5
EA949DA-122	20.5		1.2		2.7	4.1	2	31	22	21		1.35		1.5
EA949DA-123 ※ 23	21.4		1.2		2.9	4.5	2	32.5	23	22		1.35		1.5
EA949DA-124	22.2		1.2		3.1	4.2	2	33	24	22.9	0	1.35		1.7
EA949DA-125	23.2	±0.2	1.2	±0.06	3.1	4.3	2	34	25	23.9	-0.21	1.35	+0.14	1.7
EA949DA-126	24.2		1.2		3.1	4.4	2	35	26	24.9		1.35	0	1.7
EA949DA-127 ※ 27	25		1.2		3.3	4.5	2	36	27	25.8		1.35		1.8
EA949DA-128	25.9		1.5		3.1	4.6	2	38	28	26.6		1.65		2.1
EA949DA-129	26.9		1.5		3.5	4.7	2	39	29	27.6		1.65		2.1
EA949DA-130	27.9		1.5		3.5	4.8	2	40	30	28.6		1.65		2.1
EA949DA-132	29.6		1.5		3.5	5	2.5	43	32	30.3		1.65		2.6
EA949DA-134	31.5		1.5		4	5.3	2.5	45	34	32.3		1.65		2.6
EA949DA-135	32.2	±0.25	1.5		4	5.4	2.5	46	35	33		1.65		3
EA949DA-136 ○ 36	33.2		1.75		4	5.4	2.5	47	36	34		1.9		3
EA949DA-138 ○ 38	35.2		1.75		4.5	5.6	2.5	50	38	36		1.9		3
EA949DA-140 ○ 40	37		1.75		4.5	5.8	2.5	53	40	38	0	1.9		3
EA949DA-142 ○ 42	38.5		1.75		4.5	6.2	2.5	55	42	39.5	-0.25	1.9		3.8
EA949DA-145 ○ 45	41.5		1.75		4.8	6.3	2.5	58	45	42.5		1.9		3.8
EA949DA-147 ※ 47	43.4	±0.4	1.75	±0.07	5	6.6	2.5	61	47	44.5		1.9		3.8
EA949DA-148 ○ 48	44.5		1.75		4.8	6.5	2.5	62	48	45.5		1.9		3.8
EA949DA-150	45.8		2		5	6.7	2.5	64	50	47		2.2		4.5
EA949DA-152	47.8		2		5	6.8	2.5	66	52	49		2.2		4.5
EA949DA-155	50.8	±0.45	2		5	7	2.5	70	55	52	0	2.2		4.5
EA949DA-156	51.8		2		5	7	2.5	71	56	53	-0.3	2.2		4.5

軸用C形止め輪《STW-58~300》



単位：mm

サイズNo. STW-	止 め 輪								d4 (参考)	適 用 す る 軸						
	d3		t		b	a	d0	d1		d2		m		参考n		
	基本寸法	公 差	基本寸法	公 差	約	約	最小			基本寸法	公 差	基本寸法	公 差	最小		
EA949DA-158	58	53.8	±0.45	2	±0.07	5.5	7.1	2.5	73	58	55	0 -0.3	2.2	+0.14 0	4.5	
EA949DA-160	60	55.8		2		5.5	7.2	2.5	75	60	57		2.2		4.5	
EA949DA-162	62	57.8		2		5.5	7.2	2.5	77	62	59		2.2		4.5	
EA949DA-163	63	58.8		2		5.5	7.3	2.5	78	63	60		2.2		4.5	
EA949DA-165	65	60.8		2.5	±0.08	6.4	7.4	2.5	81	65	62		2.7	4.5		
EA949DA-168	68	63.5		2.5		6.4	7.8	2.5	84	68	65		2.7	4.5		
EA949DA-170	70	65.5		2.5		6.4	7.8	2.5	86	70	67		2.7	4.5		
EA949DA-172	72	67.5		2.5		7	7.9	2.5	88	72	69		2.7	4.5		
EA949DA-175	75	70.5		2.5		7	7.9	2.5	92	75	72		2.7	4.5		
EA949DA-178	78	73.5		2.5		7.4	8.1	2.5	95	78	75		2.7	4.5		
EA949DA-180	80	74.5		2.5		7.4	8.2	2.5	97	80	76.5		2.7	5.3		
EA949DA-182	82	76.5		2.5		7.4	8.3	3	99	82	78.5		2.7	5.3		
EA949DA-185	85	79.5	3	±0.55	8	8.4	3	103	85	81.5	0 -0.35	3.2	+0.18 0	5.3		
EA949DA-188	88	82.5	3		8	8.6	3	106	88	84.5		3.2		5.3		
EA949DA-190	90	84.5	3		8	8.7	3	108	90	86.5		3.2		5.3		
EA949DA-195	95	89.5	3		8.6	9.1	3	114	95	91.5		3.2		5.3		
EA949DA-1100	100	94.5	3		9	9.5	3	119	100	96.5	3.2	5.3				
EA949DA-1105	105	98	4		9.5	9.8	3	125	105	101	0 -0.54	4.2		0	6	
EA949DA-1110	110	103	4		9.5	10	3	131	110	106		4.2			6	
EA949DA-1115	115	108	4		9.5	10.5	3	137	115	111		4.2			6	
EA949DA-1120	120	113	4		10.3	10.9	3	143	120	116		4.2			6	
EA949DA-1125	125	118	4		10.3	11.3	3.5	148	125	121	0 -0.63	4.2		+0.2 0	6	
EA949DA-1130	130	123	4		11	11.5	3.5	154	130	126		4.2			6	
EA949DA-1135	135	128	4		11	11.5	3.5	159	135	131		4.2			6	
EA949DA-1140	140	133	4	11	11.8	3.5	164	140	136	4.2		6				
EA949DA-1145	145	138	4	11.6	11.8	3.5	170	145	141	4.2		6				
EA949DA-1150	150	142	4	11.6	12.3	3.5	175	150	145	4.2		7.5				
EA949DA-1155	155	146	4	12.2	12.7	3.5	181	155	150	4.2		7.5				
EA949DA-1160	160	151	4	12.2	12.9	3.5	186	160	155	4.2		7.5				
EA949DA-1165	165	155.5	4	12.9	13.1	3.5	192	165	160	4.2		7.5				
EA949DA-1170	170	160.5	4	12.9	—	4	197	170	165	4.2		7.5				
EA949DA-1175	175	165.5	4	12.9	—	4	202	175	170	4.2		7.5				
EA949DA-1180	180	170.5	4	13.5	—	4	208	180	175	4.2		7.5				
EA949DA-1185	185	175.5	4	13.5	—	4	213	185	180	4.2	7.5					
EA949DA-1190	190	180.5	4	14	—	4	219	190	185	0 -0.72	4.2	+0.25 0	7.5			
EA949DA-1195	195	185.5	4	14	—	4	224	195	190		4.2		7.5			
EA949DA-1200	200	190.5	4	14	—	4	229	200	195		4.2		7.5			
EA949DA-1210	210	198	5	±0.15	14	—	4	239	210		204		5.2	9		
EA949DA-1220	220	208	5		14	—	4	249	220		214		5.2	9		
EA949DA-1230	230	218	5		14	—	4	259	230		224		5.2	9		
EA949DA-1240	240	228	5		14	—	4	269	240		234		5.2	9		
EA949DA-1250	250	238	5		14	—	4	279	250		244		5.2	9		
EA949DA-1260	260	245	5		16	—	4	293	260		252		0 -0.81	5.2	0	12
EA949DA-1270	270	255	5		16	—	4	303	270		262			5.2		12
EA949DA-1280	280	265	5		16	—	4	313	280		272			5.2		12
EA949DA-1290	290	275	5	16	—	4	323	290	282		5.2			12		
EA949DA-1300	300	285	5	16	—	4	333	300	292	5.2	12					

材質:ばね用鋼 硬さ:44~53HRC 表面処理:ACP(焼酸塩被膜)

注意点

- ※印及びSTW-130以上はオチアイ規格です。また、○印は旧JIS規格になります。
- 市場性の無い製品は在庫が無い場合があります。ご採用の際は事前にご確認ください。