


[ステンレス製]六角頭全ねじボルト
EA949LC-305~850



●材質…ステンレス

品番	呼び	サイズ(mm)					入数	重量(g) (1本)
		ℓ	ピッチ	k	s	e		
EA949LC-305	M3	5	0.50	2.00	5.50	6.40	12	0.6
EA949LC-306		6					0.7	
EA949LC-308		8					0.7	
EA949LC-310		10					0.8	
EA949LC-312		12					0.9	
EA949LC-314		14					1.0	
EA949LC-315		15					1.1	
EA949LC-316		16					1.1	
EA949LC-318		18					1.2	
EA949LC-320		20					1.3	
EA949LC-325		25					1.6	
EA949LC-330		30					1.9	
EA949LC-335		35					2.2	
EA949LC-340		40					2.5	
EA949LC-345		45					2.6	
EA949LC-350		50					2.8	
EA949LC-406	M4	6	0.70	2.80	7.00	8.10	17	1.4
EA949LC-408		8					1.5	
EA949LC-410		10					1.7	
EA949LC-412		12					1.8	
EA949LC-414		14					2.0	
EA949LC-415		15					2.1	
EA949LC-416		16					2.2	
EA949LC-418		18					2.3	
EA949LC-420		20					2.5	
EA949LC-422		22					2.6	
EA949LC-425		25					2.7	
EA949LC-430		30					3.2	
EA949LC-435		35					3.6	
EA949LC-440		40					4.0	
EA949LC-445		45					4.4	
EA949LC-450		50					4.8	

品番	呼び	サイズ(mm)					入数	重量(g) (1本)	
		ℓ	ピッチ	k	s	e			
EA949LC-506	M5	6	0.80	3.50	8.00	9.20	14	2.3	
EA949LC-508		8					15	2.5	
EA949LC-510		10					14	2.7	
EA949LC-512		12					13	2.9	
EA949LC-514		14					11	3.1	
EA949LC-515		15					12	3.3	
EA949LC-516		16							3.4
EA949LC-518		18					11	3.5	
EA949LC-520		20						3.9	
EA949LC-522		22						9	4.3
EA949LC-525		25					4.5		
EA949LC-530		30					5.5		
EA949LC-535		35					8	5.8	
EA949LC-540		40					7	6.4	
EA949LC-545		45					6	7.0	
EA949LC-550		50						7.4	
EA949LC-608		M6					8	1.00	4.00
EA949LC-610	10		13	4.4					
EA949LC-612	12		15	4.7					
EA949LC-614	14		12	5.1					
EA949LC-615	15		13	5.2					
EA949LC-616	16			5.4					
EA949LC-618	18		12	5.8					
EA949LC-620	20			6.2					
EA949LC-622	22		10	6.5					
EA949LC-625	25			6.7					
EA949LC-628	28		5	7.2					
EA949LC-630	30		9	8.4					
EA949LC-632	32		5	8.8					
EA949LC-635	35		8	9.5					
EA949LC-640	40		7	10.6					
EA949LC-645	45			11.7					
EA949LC-650	50		6	12.9					
EA949LC-810	M8	10	1.25	5.50	13.00	15.00	5	9.4	
EA949LC-812		12						10.0	
EA949LC-814		14					6	10.6	
EA949LC-815		15							10.9
EA949LC-816		16							11.2
EA949LC-818		18							11.8
EA949LC-820		20							13.1
EA949LC-822		22					5	13.1	
EA949LC-825		25						14.3	
EA949LC-828		28					3	15.6	
EA949LC-830		30					4	16.2	
EA949LC-832		32					3	16.9	
EA949LC-835		35					4	18.2	
EA949LC-840		40						20.2	
EA949LC-845		45					3	22.2	
EA949LC-850		50						24.1	