

EA986GE-75



EAN: 4047526288952

ID: 288951

Light duty swivel castor with bolt hole fitting, Wheel with solid rubber tyres, with synthetic rim


Bracket:

Made of pressed steel, with double ball bearing in the swivel head, strong central kingpin, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation. Tread colour: dark grey

Rim / wheel centre: Made of high-quality, impact-resistant nylon. Pressed-on tyre.



Technical data

| | |
|-------------------------|-------------|
| Wheel Ø (D) | 75 mm |
| Wheel width (T2) | 25 mm |
| Load capacity | 60 kg |
| Total height (H) | 98 mm |
| Offset swvl castor (F) | 29 mm |
| Unit weight | 0.314 kg |
| Temperature range from | -20 °C |
| Temperature range to | 60 °C |
| Tread & tyre hardness | 80° Shore A |
| Bearing type | |
| Plate size (A,B) | 43 mm |
| Bolt hole Ø (d) | 11 mm |
| Bolt hole spacing (a,b) | mm |

Rolling resistance



Operating noise



Floor surface preservation



LRA-VPA 75K-ES

| Variants | |
|------------------------------------------------------------------------------------|----------------------------------------------|
|  | Antistatic version |
|  | With pressed steel thread guard, zinc-plated |
|  | Threaded pin M10 x 20 |