



P/N	SIZE	A	B	C
50001	M2 - M4 (#2 - #8)	104	50	5
50002	M3 - M14 (#4 - 1/2")	110	62	15
50003	M4 - M24 (#6 - 1")	120	67	25
50004	M20 - M39 (7/8" - 1-1/2")	147	102	38
50005	M38 - M65 (1-1/2" - 2-1/2")	161	180	64

EA949VK-3
EA949VK-4

P/N 50002 - 50005



P/N 50001



NOTES:

1. DIMENSIONS ARE IN mm UNLESS OTHERWISE STATED
2. DIMENSIONS PROVIDED FOR REFERENCE ONLY

A	RELEASE FOR MANUFACTURE	CH	18/12/2019
REV.	REVISION DESCRIPTION	ZONE	INT. DATE

3rd ANGLE PROJECTION DO NOT SCALE DRAWING UNLESS OTHERWISE STATED ALL DIMENSIONS IN mm GENERAL TOLERANCES: X ± 0.50 X.X ± 0.10 X.XX ± 0.05 ANG ± 0.5°		TITLE	TANGED INSERT EXTRACTION TOOL		
		DWG	A5000X00 (SHEET1)	PART	A5000X00
		SCALE 1:1	SHEET 1 OF 1	A4	

6 5 4 3 2 1

6 5 4 3 2 1

D

D

C

C

B

B

A

A