

Product Data Sheet



LKRA-TPA 126K-FI-FK

EAN 4047526575243

ID 575241

Light duty swivel castor with bolt hole fitting with 'stop-fix' brake, Wheel with thermoplastic rubber tread, with polypropylene wheel centre

Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality thermoplastic rubber elastomer (TPE), high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, chemically bonded for an inseparable connection to the wheel centre.

Tread/tyre:

Made of thermoplastic rubber elastomer (TPE), contains traces of oil.

Tread colours: grey

Wheel centre/rim:

Made of high-quality, impact-resistant polypropylene. Chemically bonded.

Wheel centre colour: grey



Rolling resistance

■■■■□ Very good

Operating noise

■■■□□ Good

Floor surface preservation

■■■□□ Good

Product Data Sheet



Technical data

| | | |
|---------------------------|--|--------------|
| Plate size | | 57 |
| Bolt hole Ø | | 13 |
| Wheel Ø | | 125 mm (D) |
| Wheel width | | 32 mm (T2) |
| Load capacity | | 120 kg |
| Total height | | 158 mm (H) |
| Offset swivel castor | | 40 mm |
| unit weight | | 0,8 kg |
| Temperature resistance | | -20 ° C |
| Temperature resistance to | | 60 ° C |
| tread and tyre hardness | | 85° Shore A |
| Bearing type: | | Ball bearing |

