




厚さ寸法 (mm)	61-1	61-2	61-3	61-4
1以上 1以下	0.02	0.05	0.10	0.30
4.0以上 1.0以下	0.03	0.07	0.20	0.50
1.0以上 0.3以下	0.05	0.10	0.30	0.70
0.3以上 0.1以下	0.10	0.20	0.50	1.20

材料	数量	単位	備考	図面



設定トルク 50kgh. cm

9	シャフト	SUS303	φ8	1		切削																	
8	フリクション	SUS301 1/2H	±0.5	2																			
7	フリクション	FC2020H		2		三菱化学工業																	
6	フリクション本体	SUS301 1/2H	±1.2	2																			
5	フリクション	SUS304 2B	±1.2	2																			
4	スプリング	SUS	φ5	2																			
3	スプリングA	POM		2		黒色																	
2	ヒンジ A	SUS304 2B	±2.5	1	バレル研磨																		
1	ヒンジ B	SUS304 2B	±2.5	1	バレル研磨																		
<table border="1"> <tr> <td>図</td> <td>名</td> <td>図</td> <td>名</td> <td>図</td> <td>名</td> <td>図</td> <td>名</td> </tr> <tr> <td>1</td> <td>1</td> <td>2</td> <td>2</td> <td>3</td> <td>3</td> <td>4</td> <td>4</td> </tr> </table>							図	名	図	名	図	名	図	名	1	1	2	2	3	3	4	4	
図	名	図	名	図	名	図	名																
1	1	2	2	3	3	4	4																
				図種	SFTH-05																		
				図名	φ8フラットヒンジ																		
<table border="1"> <tr> <td>1</td> <td>1</td> <td>2</td> <td>2</td> <td>3</td> <td>3</td> <td>4</td> <td>4</td> </tr> <tr> <td>1</td> <td>1</td> <td>2</td> <td>2</td> <td>3</td> <td>3</td> <td>4</td> <td>4</td> </tr> </table>				1	1	2	2	3	3	4	4	1	1	2	2	3	3	4	4	図番			
1	1	2	2	3	3	4	4																
1	1	2	2	3	3	4	4																