

EA986GE-50



EAN: 4047526287665

ID: 287664

**Light duty swivel castor with bolt hole fitting, Wheel with solid rubber tyres, with synthetic rim**

**Bracket:**

Made of pressed steel, with double ball bearing in the swivel head, strong central kingpin, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.


**Wheels:**

**Tyre & running tread:** Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation. Tread colour: dark grey

**Rim / wheel centre:** Made of high-quality, impact-resistant nylon. Pressed-on tyre.

**Variants:**

mit verzinktem Stahl-Einsteckstift Ø 11x19,5 mm



Technical data

Wheel Ø (D)	50 mm
Wheel width (T2)	18 mm
Load capacity	40 kg
Total height (H)	69 mm
Offset swvl castor (F)	25 mm
Unit weight	0.214 kg
Temperature range from	-20 °C
Temperature range to	60 °C
Tread & tyre hardness	80° Shore A
Bearing type	
Plate size (A,B)	43 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	mm

Rolling resistance



Operating noise



Floor surface preservation



LRA-VPA 50K-ES

Variants	
	Antistatic version
	With zinc-plated steel plug-in pin $\varnothing$ 11x19.5 mm
	Threaded pin M10 x 20