

# Product Data Sheet



## LDA-POA 50G-FI

EAN 4047526280420  
ID 280420

Light duty twin wheel swivel castor with top plate fitting and ‘stop-fix’ brake, Nyl wheel

**Bracket:**

Made of pressed steel, with double ball bearing in the swivel head, ball protection by th special top plate and ball disc design, dynamically pressed swivel head. Bolted wheel a Zinc-plated, blue-passivated, Cr6-free.



**Wheels:**

Made of high-quality, impact-resistant nylon, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance.

**Tread/tyre:** Made of high-quality, impact-resistant nylon.

**Tread colours:** black

**Wheel centre/rim:** -

**Wheel centre colour:** grey

**Rolling resistance**

■ ■ ■ ■ ■ Excellent

**Operating noise**

■ ■ □ □ □ Satisfactory

**Floor surface preservation**

■ ■ □ □ □ Satisfactory

# Product Data Sheet



## Technical data

|                           |                                                                                     |                |
|---------------------------|-------------------------------------------------------------------------------------|----------------|
| Plate size                |    | 60 x 60        |
| Bolt hole spacing         |    | 38x38/48x48    |
| Bolt hole Ø               |    | 6,2            |
| Wheel Ø                   |    | 50 mm (D)      |
| Wheel width               |    | 2 x 18 mm (T2) |
| Load capacity             |    | 80 kg          |
| Total height              |    | 71 mm (H)      |
| Offset swivel castor      |    | 31 mm          |
| unit weight               |    | 0,3 kg         |
| Temperature resistance    |    | -25 ° C        |
| Temperature resistance to |   | 80 ° C         |
| tread and tyre hardness   |                                                                                     | 70° Shore D    |
| Bearing type              |  | Plain bore     |

