

EA986GP-125



EAN: 4047526575366

ID: 575365

Light duty fixed castor with top plate fitting, Wheel with thermoplastic rubber tread, with polypropylene wheel centre


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality thermoplastic rubber elastomer (TPE), high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, chemically bonded for an inseparable connection to the wheel centre. Tread colour: grey

Rim / wheel centre: Made of high-quality, impact-resistant polypropylene. Chemically bonded.



Technical data

Wheel Ø (D)	125 mm
Wheel width (T2)	32 mm
Load capacity	120 kg
Total height (H)	161 mm
Unit weight	0.597 kg
Temperature range from	-20 °C
Temperature range to	60 °C
Tread & tyre hardness	85° Shore A
Bearing type	
Plate size (A,B)	90 x 66 mm
Bolt hole Ø (d)	8,5 mm
Bolt hole spacing (a,b)	75x45/61x51 mm

Rolling resistance



Operating noise



Floor surface preservation



BKPA-TPA 126K-FK

Variants



Electrically conductive
version, non-marking