

## EA986HH-200



**EAN: 4047526035983**

**ID: 35980**

**Pressed steel swivel castor, medium heavy duty brackets, with top plate fitting, Wheel with pneumatic tyres, with pressed steel rim**


**Bracket:**

Made of heavy pressed steel, with double ball bearing in the swivel head, strong central kingpin, swivel head seals. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

**Wheels:**

**Tyre & running tread:** Pneumatic tyre with tube, outstandingly high operational comfort, exceptionally high floor preservation, PAH conform acc. to EU directive 2005/69/EC. Tread colour: black

**Rim / wheel centre:** Made of pressed steel, with tubular steel hub, zinc-plated, blue-passivated, Cr6-free. Tyre mounted on rim.



### Technical data

Wheel Ø (D)	200 mm
Wheel width (T2)	50 mm
Profile	R01
Load capacity	75 kg
Total height (H)	235 mm
Offset swvl castor (F)	65 mm
Unit weight	2.465 kg
Temperature range from	-25 °C
Temperature range to	50 °C
Tread & tyre hardness	65° Shore A
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm

Rolling resistance





Operating noise



Floor surface preservation



**L-P 200R**

Variants	
	With non-marking grey tyre
	With 'stop-top' brake