

EA986HH-260



EAN: 4047526040499

ID: 40493

Pressed steel swivel castor, medium heavy duty brackets, with top plate fitting, Wheel with pneumatic tyres, with pressed steel rim


Bracket:

Made of heavy pressed steel, with double ball bearing in the swivel head, strong central kingpin, swivel head seals. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Pneumatic tyre with tube, outstandingly high operational comfort, exceptionally high floor preservation, PAH conform acc. to EU directive 2005/69/EC. Tread colour: black

Rim / wheel centre: Made of pressed steel, with tubular steel hub, zinc-plated, blue-passivated, Cr6-free. Tyre mounted on rim.



Technical data

Wheel Ø (D)	260 mm
Wheel width (T2)	85 mm
Profile	R01
Load capacity	250 kg
Total height (H)	308 mm
Offset swvl castor (F)	78 mm
Unit weight	5.18 kg
Temperature range from	-25 °C
Temperature range to	50 °C
Tread & tyre hardness	65° Shore A
Bearing type	
Plate size (A,B)	175 x 175 mm
Bolt hole Ø (d)	15 mm
Bolt hole spacing (a,b)	140 x 140 mm

Rolling resistance



Operating noise



Floor surface preservation



L-P 265R

Variants	
	With non-marking grey tyre
	With 'stop-top' brake