

EA986HP-150



EAN: 4047526006228

ID: 6221

Pressed steel swivel castor, heavy duty castors, with top plate fitting, Nylon wheel


Bracket:

Made of heavy pressed steel, with heavy fork and top plate, very strong bolted and secured central kingpin, double ball bearing in the swivel head, additionally reinforced by the integration of four specially shaped and hardened bearing seats resulting in a very high resistance to shock and impact loads. Bolted wheel axle. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality, impact-resistant nylon. Tread colour: natural white

Rim / wheel centre: -



Technical data

Wheel Ø (D)	150 mm
Wheel width (T2)	50 mm
Load capacity	400 kg
Total height (H)	197 mm
Offset swvl castor (F)	65 mm
Unit weight	3.24 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	70° Shore D
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm


Rolling resistance





Operating noise



Floor surface preservation



LH-PO 150K

Variants	
	With pressed steel thread guard, zinc-plated
	With 'stop-top' brake