

Product Data Sheet



LH-PO 150K-ST

EAN 4047526011604

ID 11601

Pressed steel swivel castor, heavy duty castors, with top plate fitting and 'stop-top' brake, Nylon wheel

Bracket:

Made of heavy pressed steel, with heavy fork and top plate, very strong bolted and secured central kingpin, double ball bearing in the swivel head, additionally reinforced by the integration of four specially shaped and hardened bearing seats resulting in a very high resistance to shock and impact loads. Bolted wheel axle. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels: Made of high-quality, impact-resistant nylon. **Tread colours:**

natural white

Wheel centre/rim: - Wheel centre colour: natural white



Rolling resistance

■■■■■ Excellent

Operating noise

■■□□□ Satisfactory













Floor surface preservation

■■□□□ Satisfactory

Product Data Sheet



Technical data

| | | |
|---------------------------|-----------------------------------------------------------------------------------|--------------|
| Plate size |  | 140 x 110 |
| Bolt hole spacing |  | 105 x 75-80 |
| Bolt hole Ø |  | 11 |
| Wheel Ø |  | 150 mm (D) |
| Wheel width |  | 50 mm (T2) |
| Load capacity |  | 400 kg |
| Total height |  | 197 mm (H) |
| Offset swivel castor |  | 65 mm |
| unit weight |  | 3,8 kg |
| Temperature resistance |  | -25 ° C |
| Temperature resistance to |  | 80 ° C |
| tread and tyre hardness | | 70° Shore D |
| Bearing type |  | Ball bearing |

