

EA986JH-1



EAN: 4047526068851

ID: 68858

, Heavy duty wheel with super-elastic solid rubber tyre

Bracket:

Made of pressed steel, with double ball bearing in the swivel head, with strong central kingpin. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.


Wheels:

Tyre & running tread: Made of super-elastic solid rubber, tough and hard rubber core, steel-wire reinforced, very high operational comfort, good floor preservation. Tread colour: black

Rim / wheel centre: Pressed steel rim, pressed and bolted, with welded tubular steel hub, or pressed steel rim with reinforced rim version, zinc-plated, blue-passivated, Cr6-free.

Variants:

mit Feststeller "stop-top"



Technical data

Wheel Ø (D)	250 mm
Wheel width (T2)	85 mm
Profile	R50
Load capacity	450 kg
Total height (H)	295 mm
Offset swvl castor (F)	70 mm
Unit weight	9.933 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	65° Shore A
Bearing type	
Plate size (A,B)	175 x 175 mm
Bolt hole Ø (d)	15 mm
Bolt hole spacing (a,b)	140 x 140 mm

Rolling resistance



Operating noise



Floor surface preservation



Blickle Räder+Rollen GmbH u. Co. KG

Heinrich-Blickle-Straße 1 · 72348 Rosenfeld · Germany

Telefon: +49 7428 932-0 · Telefax: +49 7428 932-209

E-Mail: info@blickle.com · Internet: www.blickle.com

© Blickle Räder+Rollen GmbH u. Co. KG 2013
Rosenfeld · Germany