

EA986JW-100



EAN: 4047526587611

ID: 587618

Pressed steel extra heavy duty twin wheel compact fixed castor, heavy duty design, with top plate fitting, Heavy duty wheel with elastic solid rubber tyres 'Blickle EasyRoll', with aluminium wheel centre


Bracket:

Particularly rugged welded steel construction. Bolted wheel axle. Lacquered, red.

Wheels:

Tyre & running tread: Made of high-quality elastic solid rubber, in smooth rolling quality "Blickle EasyRoll", very high operational comfort, low-noise operation, low rolling resistance, very good floor preservation, vulcanised on the wheel centre. Tread colour: black

Rim / wheel centre: Made of die-cast aluminium. Vulcanised tyre.



Technical data

Wheel Ø (D)	100 mm
Wheel width (T2)	2 x 40 mm
Load capacity	400 kg
Total height (H)	145 mm
Unit weight	2.602 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	65° Shore A
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm

Rolling resistance



Operating noise



Floor surface preservation



BOD-ALEV 100K

Variants



Antistatic version



With non-marking grey
tyre