

## EA986JX-100



**EAN: 4047526690403**

**ID: 690404**

**Pressed steel extra heavy duty twin wheel swivel castor, with top plate fitting, Heavy duty wheel with elastic solid rubber tyres 'Blickle EasyRoll', with aluminium wheel centre**


**Bracket:**

Made of heavy pressed steel, with heavy fork and top plate, very strong bolted and secured central kingpin, double ball bearing in the swivel head, additionally reinforced by the integration of four specially shaped and hardened bearing seats resulting in a very high resistance to shock and impact loads.

**Wheels:**

**Tyre & running tread:** Made of high-quality elastic solid rubber, in smooth rolling quality "Blickle EasyRoll", very high operational comfort, low-noise operation, low rolling resistance, very good floor preservation, vulcanised on the wheel centre. Tread colour: black

**Rim / wheel centre:** Made of die-cast aluminium. Vulcanised tyre.



### Technical data

Wheel Ø (D)	100 mm
Wheel width (T2)	2 x 40 mm
Load capacity	400 kg
Total height (H)	145 mm
Offset swvl castor (F)	45 mm
Unit weight	3.28 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	65° Shore A
Bearing type	
Plate size (A,B)	110 x 140 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	75-80 x 105 mm

Rolling resistance



Operating noise



Floor surface preservation



## LHD-ALEV 100K

### Variants



Antistatic version



With non-marking grey  
tyre