

EA986KH-125



EAN: 4047526562809

ID: 562801

Welded steel heavy duty fixed castor, Heavy duty wheel with Blickle Extrathane® polyurethane tread, with aluminium wheel centre


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality, reaction-injected polyurethane-elastomer Blickle Extrathane®, low-noise operation, low rolling resistance, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre. Tread colour: light brown

Rim / wheel centre: Made of die-cast aluminium. Casted tread.



Technical data

Wheel Ø (D)	125 mm
Wheel width (T2)	54 mm
Load capacity	450 kg
Total height (H)	170 mm
Unit weight	2.764 kg
Temperature range from	-25 °C
Temperature range to	70 °C
Tread & tyre hardness	92° Shore A
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm

Rolling resistance



Operating noise



Floor surface preservation



BO-ALTH 127K

Variants



Antistatic version, non-marking grey