

## EA986KY-150



**EAN: 4047526608699**

**ID: 608695**

**Welded steel heavy duty swivel castor, strong swivel head design, Heavy duty wheels made of cast nylon**


**Bracket:**

Particularly rugged welded steel construction, with axial grooved ball bearing DIN 711 and tapered roller bearing DIN 720 in the swivel head, dust and splash-proof, fitted grease nipple, bolted and secured with a welded very strong central kingpin. Bolted wheel axle. Zinc-plated, yellow-passivated, Cr6-free.

**Wheels:**

**Tyre & running tread:** Made of high-quality, impact-resistant, hard and tough, highly compressed cast nylon with outstanding load capacity, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance. Tread colour: natural beige

**Rim / wheel centre: -**



### Technical data

Wheel Ø (D)	150 mm
Wheel width (T2)	80 mm
Load capacity	3000 kg
Total height (H)	205 mm
Offset swvl castor (F)	65 mm
Unit weight	8.67 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	80° Shore D
Bearing type	
Plate size (A,B)	175 x 140 mm
Bolt hole Ø (d)	14 mm
Bolt hole spacing (a,b)	140 x 105 mm


Rolling resistance



Operating noise



Floor surface preservation



**LS-GSPO 152K-35**

Variants	
	With directional lock 2 x 180°
	With directional lock 4 x 90°
	With 'stop-top' brake