

**BKX-POTH 100G-1**



**EAN: 4047526084288**

**ID: 754131**


**Bracket:**

Made of heavy pressed high-quality, chromium-nickel stainless steel (Material No. 1.4301/AISI 304). All parts incl. axle material are corrosion-resistant. Bolted wheel axle. Vibration-ground finished.

**Wheels:**

**Tyre & running tread:** Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre.

**Rim / wheel centre:** Made of high-quality, impact-resistant nylon.



**Technical data**

Wheel Ø (D)	100 mm
Tread width (T2)	35 mm
Load capacity	200 kg
Overall height (H)	130 mm
Unit weight	0.603 kg
Temperature range from	-25 °C
Temperature range to	70 °C
Tread & tire hardness	94° Shore A
Bearing type	Plain bore
Plate size (A,B)	100 x 85 mm
Bolt hole Ø (d)	9 mm
Bolt hole spacing (a,b)	80 x 60 mm

Rolling resistance



Operating noise



Floor surface preservation

