

EA986NA-80



EAN: 4047526007652

ID: 7658

**Pressed steel swivel castor, medium heavy duty brackets, with top plate fitting, Cast iron wheel**


**Bracket:**

Made of heavy pressed steel, with double ball bearing in the swivel head, strong central kingpin, swivel head seals. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

**Wheels:**

**Tyre & running tread:** Made of rugged grey cast iron, machined tread and tread edges, with grease nipple, exceptionally low rolling and swivel resistance, outstanding wear resistance, lacquered. Tread colour: silver grey

**Rim / wheel centre:** -




Technical data

Wheel Ø (D)	80 mm
Wheel width (T2)	25 mm
Load capacity	200 kg
Total height (H)	102 mm
Offset swvl castor (F)	38 mm
Unit weight	1.03 kg
Temperature range from	-25 °C
Temperature range to	120 °C
Tread & tyre hardness	180 - 220 HB
Bearing type	
Plate size (A,B)	100 x 85 mm
Bolt hole Ø (d)	9 mm
Bolt hole spacing (a,b)	80 x 60 mm

Rolling resistance



Operating noise



Floor surface preservation



**L-G 80G**

Variants



With 'stop-top' brake