

EA986LG-125



EAN: 4047526084349

ID: 754133

Stainless steel heavy duty fixed castor with top plate fitting, Wheel with thermoplastic polyurethane tread, with heavy nylon wheel centre


Bracket:

Made of heavy pressed high-quality, chromium-nickel stainless steel (Material No. 1.4301/AISI 304). All parts incl. axle material are corrosion-resistant. Bolted wheel axle. Vibration-ground finished.

Wheels:

Tyre & running tread: Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre. Tread colour: dark grey

Rim / wheel centre: Made of high-quality, impact-resistant nylon.



Technical data

Wheel Ø (D)	125 mm
Wheel width (T2)	35 mm
Load capacity	250 kg
Total height (H)	155 mm
Unit weight	0.742 kg
Temperature range from	-25 °C
Temperature range to	70 °C
Tread & tyre hardness	94° Shore A
Bearing type	
Plate size (A,B)	100 x 85 mm
Bolt hole Ø (d)	9 mm
Bolt hole spacing (a,b)	80 x 60 mm

Rolling resistance



Operating noise



Floor surface preservation

