



Lifting points rotatable under load

SNS bolt-on swivel, high-tensile

Working load limit up to 6.3 tonnes, threads up to M30

- ▶ TOP traceability – each swivel has a serial number for documentation tests
- ▶ Flexible! – can be swivelled 360° under load – can be tilted by 180° – loadable all-round!
- ▶ Maximum safety – safety factor 5:1

For higher working load limits see SNB, page 197



	WLL kg	Thread	Pitch	Tightening torque Nm	Dimensions in mm										Weight approx. kg	Reference no.
					A	B	C	D	E	F	G	L ₁	S1	S2		
EA987GE-30	300	M 8	1.25	6	33	30	30	38	27	14	53	14	8	16	0.3	217043
EA987GE-31	600	M 10	1.50	10	33	30	30	38	27	14	53	17	8	16	0.3	217044
EA987GE-32	1000	M 12	1.75	15	33	30	30	38	27	14	53	21	8	16	0.3	217045
EA987GE-33	1300	M 14	2.00	30	45	42	45	54	38	17	76	23	8	20	0.9	217046
EA987GE-34	1600	M 16	2.00	50	45	42	45	54	38	17	76	27	8	20	0.9	217047
EA987GE-35	2000	M 18	2.50	70	45	42	45	54	38	17	76	27	8	20	0.9	217048
EA987GE-36	2500	M 20	2.50	100	45	42	45	54	38	17	76	30	8	20	0.9	217049
EA987GE-37	3000	M 22	2.50	120	63	55	60	83	55	25	107	33	14	24	2.6	217050
EA987GE-38	4000	M 24	3.00	160	62	55	60	83	55	25	107	36	14	24	2.6	217051
EA987GE-39	5000	M 27	3.00	200	62	55	60	83	55	25	107	40	14	24	2.7	217052
EA987GE-40	6300	M 30	3.50	250	62	55	60	83	55	25	107	45	14	24	2.7	217053

Stainless steel version and imperial thread available as standard. Please enquire!

Maximum load weight G in tonnes for different types of attachment

Type of attachment									
Number of lifting points	1	1	2	2	2 symmetrically		3 & 4 symmetrically		2, 3 & 4 asym.
Angle	0°	90°	0°	90°	0–45°	45–60°	0–45°	45–60°	
M8	0.6	0.3	1.2	0.6	0.4	0.3	0.6	0.5	0.3
M10	1.0	0.6	2.0	1.2	0.8	0.6	1.3	0.9	0.6
M12	1.5	1.0	3.0	2.0	1.4	1.0	2.1	1.5	1.0
M14	2.5	1.3	5.0	2.6	1.8	1.3	2.7	2.0	1.3
M16	3.0	1.6	6.0	3.2	2.2	1.6	3.4	2.4	1.6
M18	3.0	2.0	6.0	4.0	2.8	2.0	4.2	3.0	2.0
M20	3.0	2.5	6.0	5.0	3.5	2.5	5.3	3.8	2.5
M22	3.2	3.0	6.4	6.0	4.2	3.0	6.3	4.5	3.0
M24	5.0	4.0	10.0	8.0	5.6	4.0	8.4	6.0	4.0
M27	5.0	5.0	10.0	10.0	7.0	5.0	10.5	7.5	5.0
M30	6.3	6.3	12.6	12.6	8.8	6.3	13.2	9.5	6.3