

EA986N-250



EAN: 4047526007966

ID: 7963

Pressed steel fixed castor, heavy duty brackets, with top plate fitting, Cast iron wheel


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of rugged grey cast iron, machined tread and tread edges, with grease nipple, exceptionally low rolling and swivel resistance, outstanding wear resistance, lacquered. Tread colour: silver grey

Rim / wheel centre: -



Technical data

Wheel Ø (D)	250 mm
Wheel width (T2)	60 mm
Load capacity	900 kg
Total height (H)	295 mm
Unit weight	9.63 kg
Temperature range from	-25 °C
Temperature range to	120 °C
Tread & tyre hardness	180 - 220 HB
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm

Rolling resistance



Operating noise



Floor surface preservation

