

EA991CZ-1~100 グリースニップル



各10個入り


PF (G)			メトリック		
品番	形状	ねじサイズ	品番	形状	ねじサイズ
EA991CZ-1	ストレーツ	PF1/8"	EA991CZ-6	ストレーツ	6mm X P1.0
EA991CZ-13G	ストレーツ	PF3/8"	EA991CZ-8	ストレーツ	8mm X P1.25
EA991CZ-61	67.5°	PF1/8"	EA991CZ-10A	ストレーツ	10mm X P1.0
EA991CZ-63	67.5°	PF3/8"	EA991CZ-66	67.5°	6mm X P1.0
EA991CZ-91	90°	PF1/8"	EA991CZ-68	67.5°	8mm X P1.25
EA991CZ-93	90°	PF3/8"	EA991CZ-70	67.5°	10mm X P1.0
			EA991CZ-96	90°	6mm X P1.0
			EA991CZ-98	90°	8mm X P1.25
			EA991CZ-100	90°	10mm X P1.0

PT (R)			UNF・NPT		
品番	形状	ねじサイズ	品番	形状	ねじサイズ
EA991CZ-11	ストレーツ	PT1/8"	EA991CZ-42F	ストレーツ	UNF1/4"
EA991CZ-12	ストレーツ	PT1/4"	EA991CZ-41N	ストレーツ	NPT1/8"
EA991CZ-13	ストレーツ	PT3/8"	EA991CZ-42N	ストレーツ	NPT1/4"
EA991CZ-21	67.5°	PT1/8"	EA991CZ-72	67.5°	UNF1/4"
EA991CZ-22	67.5°	PT1/4"	EA991CZ-71N	67.5°	NPT1/8"
EA991CZ-31	90°	PT1/8"	EA991CZ-92F	90°	UNF1/4"
EA991CZ-32	90°	PT1/4"			

PT = Rねじ


PF = Gねじ

- 工作機械、ベアリングなどの摩耗箇所に取付けます。グリスポンプ等でグリスアップを行います。
- JIS規格品
- 材質 真鍮(黄銅棒)(ニッケルメッキ)




◆ JIS 相当品 (R ネジ)

A 型



呼び D	寸法		
	H	S	B×C
M6×1.0	13.5	5	7
R1/8	20	9	10
R1/4	25	12	14
R3/8	26	12	17
NPT1/8	20	9	10
NPT1/4	25	12	14
M10X1.0	20	9	10

B 型



呼び D	寸法		
	H	S	B×C
R1/8	21.5	8	10
R1/4	25	11	14
NPT1/8	21.5	8	10
M10X1.0	21	8	10


C 型



呼び D	寸法		
	H	S	B×C
R1/8	21.5	8	10
R1/4	25	11	14
M10X1.0	21	8	10


◆ 規格頭 (G ネジ)

A 型




呼び D	寸法		
	H	S	B×C
M6×1.0	13.5	5	7
M8×1.25	15.5	5.5	10
U1/4×28山	13.5	5	7
G1/8	15.5	6	10
G3/8	24.5	10.5	17

B 型



呼び D	寸法		
	H	S	B×C
M6×0.75	16.5	5	8
M6×1.0	16.5	5	8
M8×1.25	16	5.5	10
U1/4×28山	16.5	5	8
G1/8	15.5	5.5	10
G3/8	22	8.5	17

C 型



呼び D	寸法		
	H	S	B×C
M6×1.0	17.5	5	8
M8×1.25	17.5	5.5	10
U1/4×28山	17.5	5	8
G1/8	17	5.5	10
G3/8	22	8.5	17