



Air Actuated Bottle Jacks

All air bottle jacks have chrome plated rams

Effortless air operation will greatly reduce operator fatigue and speed up the efficiency of garage work

U.S. Patent No. 5,946,912, a built-in by-pass device protects hydraulic system from over pumping damage

A compact yet powerful Air Turbo Motor U.S. Patent No. 6,012,377 is equipped to raise the load to the desired height efficiently, effortlessly, and safely

18204C
20 Ton Capacity

Versatile "Quick Connector" design provides for easy removal of air hose from air motor allowing compact storage or remote operation

18204C is made with welded construction which eliminates contaminants from entering hydraulic system and provides leak free operation.

18126C & 18206C
Equipped with external return springs.



18206C
20 Ton Capacity

18302C
30 Ton Capacity

18502
50 Ton Capacity

18992
100 Ton Capacity

Model	Capacity	Minimum Height	Maximum Height	Hydraulic Lifting	Extension. Screw	Base Size Length	Base Size Width	G.W.
18126C	12 Ton	9-5/8"	18-7/8"	3-1/8"	6"	8-1/8"	5-7/8"	27 Lbs.
18124C	12 Ton	9-1/2"	18-1/2"	5-1/2"	3-1/2"	7-7/8"	6-1/4"	37 Lbs.
18206C	20 Ton	9-5/8"	18-7/8"	3-1/8"	6"	9"	6-3/4"	37 Lbs.
18204C		9-3/4"	18-3/4"	5-1/8"	3-7/8"	8-1/2"	7-1/8"	37 Lbs.
18209		8-1/8"	15-1/2"	4"	3-3/8"	8-1/2"	7-1/4"	37 Lbs.
EA993CJ-3 18302C	30 Ton	11"	18-1/8"	7-1/8"	N/A	10-1/4"	8-1/4"	63 Lbs.
18502	50 Ton	12"	19"	7"		10-7/8"	7-3/8"	134.5 Lbs.
18992	100 Ton	12"	18-1/8"	6-1/8"		12-5/8"	9-3/8"	220.5 Lbs.