

## Product Data Sheet



### BS-SPK 251K

**EAN** 4047526281762

**ID** 281766

#### Welded steel heavy duty fixed castor, Cast iron flanged wheel

##### Bracket:


Particularly rugged welded steel construction with reinforced fork for an improved absorption of axial forces. Bolted wheel axle. Zinc-plated, yellow-passivated, Cr6-free.

##### Wheels:

Made of rugged grey cast iron, with grease nipple, machined tread with horizontal taper of 3°, exceptionally low rolling resistance, outstanding wear resistance, lacquered.

**Tread colours:** silver

**Wheel centre/rim: - Wheel centre colour:** silver



##### Rolling resistance

■■■■■ Excellent

##### Operating noise

■□□□□ Sufficient

##### Floor surface preservation

■□□□□ Sufficient

# Product Data Sheet



## Technical data

|                            |  |              |
|----------------------------|--|--------------|
| Plate size                 |  | 200 x 160    |
| Bolt hole spacing          |  | 160 x 120    |
| Bolt hole Ø                |  | 14           |
| Wheel Ø without flange     |  | mm (D)       |
| Wheel Ø without flange     |  | 250 mm (D)   |
| Tread width without flange |  | mm (T3)      |
| Tread width                |  | 60 mm (T3)   |
| Flange length              |  | 20 mm (T4)   |
| Load capacity              |  | 3500 kg      |
| Axle bore Ø                |  | 14 mm (d)    |
| Total height               |  | 305 mm (H)   |
| unit weight                |  | 27,4 kg      |
| Temperature resistance     |  | -25 ° C      |
| Temperature resistance to  |  | 120 ° C      |
| tread and tyre hardness    |  | 180 - 220 HB |
| Bearing type               |  | Ball bearing |

