

EA986SD-150




EAN: 4047526008536

ID: 8532

Cast iron flanged wheel

Tyre & running tread: Made of rugged grey cast iron, with grease nipple, machined tread with horizontal taper of 3°, exceptionally low rolling resistance, outstanding wear resistance, lacquered. Tread colour: silver
Rim / wheel centre: -



Technical data

Wheel Ø (D)	150 mm
Wheel Ø incl. flange (D1)	175 mm
Wheel width (T2)	46 mm
Tread width without flange (T3)	36 mm
Flange length (T4)	13 mm
Load capacity	1000 kg
Axle bore Ø (d)	20 mm
Hub length (T1)	52 mm
Unit weight	3.815 kg
Temperature range from	125 °C
Temperature range to	120 °C
Tread & tyre hardness	180 - 220 HB
Bearing type	

Rolling resistance



Operating noise



Floor surface preservation



Blickle Räder+Rollen GmbH u. Co. KG

Heinrich-Blickle-Straße 1 · 72348 Rosenfeld · Germany

Telefon: +49 7428 932-0 · Telefax: +49 7428 932-209

E-Mail: info@blickle.com · Internet: www.blickle.com

© Blickle Räder+Rollen GmbH u. Co. KG 2013
 Rosenfeld · Germany