



Grease supply system-with ZBH

20-kg-BE-Ø 270-310 mm-2 m-HS

Item number: 18 419 051
EAN: 4103810429699
Discount group: D

Technical data

Compressed air connection: Male quick release adapter, for Rectus coupling, type 26, NW 7,2 mm
Grease connection: coupler, for hydraulic grease nipples, DIN 71412

Specification

- For 20-kg-container, ø 270 - 310 mm
- Pneumatic grease pump 50:1
- Item number pneumatic grease pump: 18 711 051
- Special pump mechanism
- Male quick release adapter (20 062)
- High pressure grease gun (18 104)
- Z-swivel joint (18 082)
- Pressure reducing valve (pre-set at 8 bar)
- High pressure hose, 2 m (18 022)
- Dust cover (17 176)
- Stabilising-fixing bracket (17 197)
- Follower plate (17 300)

Packaging

Dimensions LxWxH (mm): 1010 x 480 x 105
Weight (kg): 12,24
Packing unit: 1.0