

品番 : **EA829SE-16B**

品名 : M16x1.5 スパ イラトップ° (ステンレス用・ホモ処理)



販売価格	<b>6,820円</b> (税抜) / 7,502円(税込)		
カタログ価格	6,820円(税抜) / 7,502円(税込)		
在庫数	<b>最新在庫: 1</b> (2026/06/26 00:33現在)		
商品入数	1	販売単位	本
カタログページ	0898ページ		



品名	型番	長さ	径	溝数	重量
EX-SUS-SFT STD	EA829SE-16B	95	16	3	92
EX-SUS-SFT STD	EA829SE-16C	115	16	3	115
EX-SUS-SFT STD	EA829SE-16D	135	16	3	135
EX-SUS-SFT STD	EA829SE-16E	155	16	3	155
EX-SUS-SFT STD	EA829SE-16F	175	16	3	175
EX-SUS-SFT STD	EA829SE-16G	195	16	3	195
EX-SUS-SFT STD	EA829SE-16H	215	16	3	215
EX-SUS-SFT STD	EA829SE-16I	235	16	3	235
EX-SUS-SFT STD	EA829SE-16J	255	16	3	255
EX-SUS-SFT STD	EA829SE-16K	275	16	3	275
EX-SUS-SFT STD	EA829SE-16L	295	16	3	295
EX-SUS-SFT STD	EA829SE-16M	315	16	3	315
EX-SUS-SFT STD	EA829SE-16N	335	16	3	335
EX-SUS-SFT STD	EA829SE-16O	355	16	3	355
EX-SUS-SFT STD	EA829SE-16P	375	16	3	375
EX-SUS-SFT STD	EA829SE-16Q	395	16	3	395
EX-SUS-SFT STD	EA829SE-16R	415	16	3	415
EX-SUS-SFT STD	EA829SE-16S	435	16	3	435
EX-SUS-SFT STD	EA829SE-16T	455	16	3	455
EX-SUS-SFT STD	EA829SE-16U	475	16	3	475
EX-SUS-SFT STD	EA829SE-16V	495	16	3	495
EX-SUS-SFT STD	EA829SE-16W	515	16	3	515
EX-SUS-SFT STD	EA829SE-16X	535	16	3	535
EX-SUS-SFT STD	EA829SE-16Y	555	16	3	555
EX-SUS-SFT STD	EA829SE-16Z	575	16	3	575
EX-SUS-SFT STD	EA829SE-16AA	595	16	3	595
EX-SUS-SFT STD	EA829SE-16AB	615	16	3	615
EX-SUS-SFT STD	EA829SE-16AC	635	16	3	635
EX-SUS-SFT STD	EA829SE-16AD	655	16	3	655
EX-SUS-SFT STD	EA829SE-16AE	675	16	3	675
EX-SUS-SFT STD	EA829SE-16AF	695	16	3	695
EX-SUS-SFT STD	EA829SE-16AG	715	16	3	715
EX-SUS-SFT STD	EA829SE-16AH	735	16	3	735
EX-SUS-SFT STD	EA829SE-16AI	755	16	3	755
EX-SUS-SFT STD	EA829SE-16AJ	775	16	3	775
EX-SUS-SFT STD	EA829SE-16AK	795	16	3	795
EX-SUS-SFT STD	EA829SE-16AL	815	16	3	815
EX-SUS-SFT STD	EA829SE-16AM	835	16	3	835
EX-SUS-SFT STD	EA829SE-16AN	855	16	3	855
EX-SUS-SFT STD	EA829SE-16AO	875	16	3	875
EX-SUS-SFT STD	EA829SE-16AP	895	16	3	895
EX-SUS-SFT STD	EA829SE-16AQ	915	16	3	915
EX-SUS-SFT STD	EA829SE-16AR	935	16	3	935
EX-SUS-SFT STD	EA829SE-16AS	955	16	3	955
EX-SUS-SFT STD	EA829SE-16AT	975	16	3	975
EX-SUS-SFT STD	EA829SE-16AU	995	16	3	995
EX-SUS-SFT STD	EA829SE-16AV	1015	16	3	1015
EX-SUS-SFT STD	EA829SE-16AW	1035	16	3	1035
EX-SUS-SFT STD	EA829SE-16AX	1055	16	3	1055
EX-SUS-SFT STD	EA829SE-16AY	1075	16	3	1075
EX-SUS-SFT STD	EA829SE-16AZ	1095	16	3	1095
EX-SUS-SFT STD	EA829SE-16BA	1115	16	3	1115
EX-SUS-SFT STD	EA829SE-16BB	1135	16	3	1135
EX-SUS-SFT STD	EA829SE-16BC	1155	16	3	1155
EX-SUS-SFT STD	EA829SE-16BD	1175	16	3	1175
EX-SUS-SFT STD	EA829SE-16BE	1195	16	3	1195
EX-SUS-SFT STD	EA829SE-16BF	1215	16	3	1215
EX-SUS-SFT STD	EA829SE-16BG	1235	16	3	1235
EX-SUS-SFT STD	EA829SE-16BH	1255	16	3	1255
EX-SUS-SFT STD	EA829SE-16BI	1275	16	3	1275
EX-SUS-SFT STD	EA829SE-16BJ	1295	16	3	1295
EX-SUS-SFT STD	EA829SE-16BK	1315	16	3	1315
EX-SUS-SFT STD	EA829SE-16BL	1335	16	3	1335
EX-SUS-SFT STD	EA829SE-16BM	1355	16	3	1355
EX-SUS-SFT STD	EA829SE-16BN	1375	16	3	1375
EX-SUS-SFT STD	EA829SE-16BO	1395	16	3	1395
EX-SUS-SFT STD	EA829SE-16BP	1415	16	3	1415
EX-SUS-SFT STD	EA829SE-16BQ	1435	16	3	1435
EX-SUS-SFT STD	EA829SE-16BR	1455	16	3	1455
EX-SUS-SFT STD	EA829SE-16BS	1475	16	3	1475
EX-SUS-SFT STD	EA829SE-16BT	1495	16	3	1495
EX-SUS-SFT STD	EA829SE-16BU	1515	16	3	1515
EX-SUS-SFT STD	EA829SE-16BV	1535	16	3	1535
EX-SUS-SFT STD	EA829SE-16BW	1555	16	3	1555
EX-SUS-SFT STD	EA829SE-16BX	1575	16	3	1575
EX-SUS-SFT STD	EA829SE-16BY	1595	16	3	1595
EX-SUS-SFT STD	EA829SE-16BZ	1615	16	3	1615
EX-SUS-SFT STD	EA829SE-16CA	1635	16	3	1635
EX-SUS-SFT STD	EA829SE-16CB	1655	16	3	1655
EX-SUS-SFT STD	EA829SE-16CC	1675	16	3	1675
EX-SUS-SFT STD	EA829SE-16CD	1695	16	3	1695
EX-SUS-SFT STD	EA829SE-16CE	1715	16	3	1715
EX-SUS-SFT STD	EA829SE-16CF	1735	16	3	1735
EX-SUS-SFT STD	EA829SE-16CG	1755	16	3	1755
EX-SUS-SFT STD	EA829SE-16CH	1775	16	3	1775
EX-SUS-SFT STD	EA829SE-16CI	1795	16	3	1795
EX-SUS-SFT STD	EA829SE-16CJ	1815	16	3	1815
EX-SUS-SFT STD	EA829SE-16CK	1835	16	3	1835
EX-SUS-SFT STD	EA829SE-16CL	1855	16	3	1855
EX-SUS-SFT STD	EA829SE-16CM	1875	16	3	1875
EX-SUS-SFT STD	EA829SE-16CN	1895	16	3	1895
EX-SUS-SFT STD	EA829SE-16CO	1915	16	3	1915
EX-SUS-SFT STD	EA829SE-16CP	1935	16	3	1935
EX-SUS-SFT STD	EA829SE-16CQ	1955	16	3	1955
EX-SUS-SFT STD	EA829SE-16CR	1975	16	3	1975
EX-SUS-SFT STD	EA829SE-16CS	1995	16	3	1995
EX-SUS-SFT STD	EA829SE-16CT	2015	16	3	2015
EX-SUS-SFT STD	EA829SE-16CU	2035	16	3	2035
EX-SUS-SFT STD	EA829SE-16CV	2055	16	3	2055
EX-SUS-SFT STD	EA829SE-16CW	2075	16	3	2075
EX-SUS-SFT STD	EA829SE-16CX	2095	16	3	2095
EX-SUS-SFT STD	EA829SE-16CY	2115	16	3	2115
EX-SUS-SFT STD	EA829SE-16CZ	2135	16	3	2135
EX-SUS-SFT STD	EA829SE-16DA	2155	16	3	2155
EX-SUS-SFT STD	EA829SE-16DB	2175	16	3	2175
EX-SUS-SFT STD	EA829SE-16DC	2195	16	3	2195
EX-SUS-SFT STD	EA829SE-16DD	2215	16	3	2215
EX-SUS-SFT STD	EA829SE-16DE	2235	16	3	2235
EX-SUS-SFT STD	EA829SE-16DF	2255	16	3	2255
EX-SUS-SFT STD	EA829SE-16DG	2275	16	3	2275
EX-SUS-SFT STD	EA829SE-16DH	2295	16	3	2295
EX-SUS-SFT STD	EA829SE-16DI	2315	16	3	2315
EX-SUS-SFT STD	EA829SE-16DJ	2335	16	3	2335
EX-SUS-SFT STD	EA829SE-16DK	2355	16	3	2355
EX-SUS-SFT STD	EA829SE-16DL	2375	16	3	2375
EX-SUS-SFT STD	EA829SE-16DM	2395	16	3	2395
EX-SUS-SFT STD	EA829SE-16DN	2415	16	3	2415
EX-SUS-SFT STD	EA829SE-16DO	2435	16	3	2435
EX-SUS-SFT STD	EA829SE-16DP	2455	16	3	2455
EX-SUS-SFT STD	EA829SE-16DQ	2475	16	3	2475
EX-SUS-SFT STD	EA829SE-16DR	2495	16	3	2495
EX-SUS-SFT STD	EA829SE-16DS	2515	16	3	2515
EX-SUS-SFT STD	EA829SE-16DT	2535	16	3	2535
EX-SUS-SFT STD	EA829SE-16DU	2555	16	3	2555
EX-SUS-SFT STD	EA829SE-16DV	2575	16	3	2575
EX-SUS-SFT STD	EA829SE-16DW	2595	16	3	2595
EX-SUS-SFT STD	EA829SE-16DX	2615	16	3	2615
EX-SUS-SFT STD	EA829SE-16DY	2635	16	3	2635
EX-SUS-SFT STD	EA829SE-16DZ	2655	16	3	2655
EX-SUS-SFT STD	EA829SE-16EA	2675	16	3	2675
EX-SUS-SFT STD	EA829SE-16EB	2695	16	3	2695
EX-SUS-SFT STD	EA829SE-16EC	2715	16	3	2715
EX-SUS-SFT STD	EA829SE-16ED	2735	16	3	2735
EX-SUS-SFT STD	EA829SE-16EE	2755	16	3	2755
EX-SUS-SFT STD	EA829SE-16EF	2775	16	3	2775
EX-SUS-SFT STD	EA829SE-16EG	2795	16	3	2795
EX-SUS-SFT STD	EA829SE-16EH	2815	16	3	2815
EX-SUS-SFT STD	EA829SE-16EI	2835	16	3	2835
EX-SUS-SFT STD	EA829SE-16EJ	2855	16	3	2855
EX-SUS-SFT STD	EA829SE-16EK	2875	16	3	2875
EX-SUS-SFT STD	EA829SE-16EL	2895	16	3	2895
EX-SUS-SFT STD	EA829SE-16EM	2915	16	3	2915
EX-SUS-SFT STD	EA829SE-16EN	2935	16	3	2935
EX-SUS-SFT STD	EA829SE-16EO	2955	16	3	2955
EX-SUS-SFT STD	EA829SE-16EP	2975	16	3	2975
EX-SUS-SFT STD	EA829SE-16EQ	2995	16	3	2995
EX-SUS-SFT STD	EA829SE-16ER	3015	16	3	3015
EX-SUS-SFT STD	EA829SE-16ES	3035	16	3	3035
EX-SUS-SFT STD	EA829SE-16ET	3055	16	3	3055
EX-SUS-SFT STD	EA829SE-16EU	3075	16	3	3075
EX-SUS-SFT STD	EA829SE-16EV	3095	16	3	3095
EX-SUS-SFT STD	EA829SE-16EW	3115	16	3	3115
EX-SUS-SFT STD	EA829SE-16EX	3135	16	3	3135
EX-SUS-SFT STD	EA829SE-16EY	3155	16	3	3155
EX-SUS-SFT STD	EA829SE-16EZ	3175	16	3	3175
EX-SUS-SFT STD	EA829SE-16FA	3195	16	3	3195
EX-SUS-SFT STD	EA829SE-16FB	3215	16	3	3215
EX-SUS-SFT STD	EA829SE-16FC	3235	16	3	3235
EX-SUS-SFT STD	EA829SE-16FD	3255	16	3	3255
EX-SUS-SFT STD	EA829SE-16FE	3275	16	3	3275
EX-SUS-SFT STD	EA829SE-16FF	3295	16	3	3295
EX-SUS-SFT STD	EA829SE-16FG	3315	16	3	3315
EX-SUS-SFT STD	EA829SE-16FH	3335	16	3	3335
EX-SUS-SFT STD	EA829SE-16FI	3355	16	3	3355
EX-SUS-SFT STD	EA829SE-16FJ	3375	16	3	3375
EX-SUS-SFT STD	EA829SE-16FK	3395	16	3	3395
EX-SUS-SFT STD	EA829SE-16FL	3415	16	3	3415
EX-SUS-SFT STD	EA829SE-16FM	3435	16	3	3435
EX-SUS-SFT STD	EA829SE-16FN	3455	16	3	3455
EX-SUS-SFT STD	EA829SE-16FO	3475	16	3	3475
EX-SUS-SFT STD	EA829SE-16FP	3495	16	3	3495
EX-SUS-SFT STD	EA829SE-16FQ	3515	16	3	3515
EX-SUS-SFT STD	EA829SE-16FR	3535	16	3	3535
EX-SUS-SFT STD	EA829SE-16FS	3555	16	3	3555
EX-SUS-SFT STD	EA829SE-16FT	3575	16	3	3575
EX-SUS-SFT STD	EA829SE-16FU	3595	16	3	3595
EX-SUS-SFT STD	EA829SE-16FV	3615	16	3	3615
EX-SUS-SFT STD	EA829SE-16FW	3635	16	3	3635
EX-SUS-SFT STD	EA829SE-16FX	3655	16	3	3655
EX-SUS-SFT STD	EA829SE-16FY	3675	16	3	3675
EX-SUS-SFT STD	EA829SE-16FZ	3695	16	3	3695
EX-SUS-SFT STD	EA829SE-16GA	3715	16	3	3715
EX-SUS-SFT STD	EA829SE-16GB	3735	16	3	3735
EX-SUS-SFT STD	EA829SE-16GC	3755	16	3	3755
EX-SUS-SFT STD	EA829SE-16GD	3775	16	3	3775
EX-SUS-SFT STD	EA829SE-16GE	3795	16	3	3795
EX-SUS-SFT STD	EA829SE-16GF	3815	16	3	3815
EX-SUS-SFT STD	EA829SE-16GG	3835	16	3	3835
EX-SUS-SFT STD	EA829SE-16GH	3855	16	3	3855
EX-SUS-SFT STD	EA829SE-16GI	3875	16	3	3875
EX-SUS-SFT STD	EA829SE-16GJ	3895	16	3	3895
EX-SUS-SFT STD	EA829SE-16GK	3915	16	3	3915
EX-SUS-SFT STD	EA829SE-16GL	3935	16	3	3935
EX-SUS-SFT STD	EA829SE-16GM	3955	16	3	3955