

品番：EA829SE-10

品名：M10x1.5 スパ イラトップ° (ステンレス用・ホモ処理)



|         |                              |      |   |
|---------|------------------------------|------|---|
| 販売価格    | 2,590円(税抜) / 2,849円(税込)      |      |   |
| カタログ価格  | 2,590円(税抜) / 2,849円(税込)      |      |   |
| 在庫数     | 最新在庫: 2 (2026/06/26 03:09現在) |      |   |
| 商品入数    | 1                            | 販売単位 | 本 |
| カタログページ | 0898ページ                      |      |   |



| 品名             | 型番          | 長さ   | 径  | 溝数 | 重量   |
|----------------|-------------|------|----|----|------|
| EX-SUS-SFT STD | EA829SE-10  | 75   | 10 | 3  | 26   |
| EX-SUS-SFT STD | EA829SE-15  | 90   | 10 | 3  | 32   |
| EX-SUS-SFT STD | EA829SE-20  | 105  | 10 | 3  | 38   |
| EX-SUS-SFT STD | EA829SE-25  | 120  | 10 | 3  | 44   |
| EX-SUS-SFT STD | EA829SE-30  | 135  | 10 | 3  | 50   |
| EX-SUS-SFT STD | EA829SE-35  | 150  | 10 | 3  | 56   |
| EX-SUS-SFT STD | EA829SE-40  | 165  | 10 | 3  | 62   |
| EX-SUS-SFT STD | EA829SE-45  | 180  | 10 | 3  | 68   |
| EX-SUS-SFT STD | EA829SE-50  | 195  | 10 | 3  | 74   |
| EX-SUS-SFT STD | EA829SE-55  | 210  | 10 | 3  | 80   |
| EX-SUS-SFT STD | EA829SE-60  | 225  | 10 | 3  | 86   |
| EX-SUS-SFT STD | EA829SE-65  | 240  | 10 | 3  | 92   |
| EX-SUS-SFT STD | EA829SE-70  | 255  | 10 | 3  | 98   |
| EX-SUS-SFT STD | EA829SE-75  | 270  | 10 | 3  | 104  |
| EX-SUS-SFT STD | EA829SE-80  | 285  | 10 | 3  | 110  |
| EX-SUS-SFT STD | EA829SE-85  | 300  | 10 | 3  | 116  |
| EX-SUS-SFT STD | EA829SE-90  | 315  | 10 | 3  | 122  |
| EX-SUS-SFT STD | EA829SE-95  | 330  | 10 | 3  | 128  |
| EX-SUS-SFT STD | EA829SE-100 | 345  | 10 | 3  | 134  |
| EX-SUS-SFT STD | EA829SE-105 | 360  | 10 | 3  | 140  |
| EX-SUS-SFT STD | EA829SE-110 | 375  | 10 | 3  | 146  |
| EX-SUS-SFT STD | EA829SE-115 | 390  | 10 | 3  | 152  |
| EX-SUS-SFT STD | EA829SE-120 | 405  | 10 | 3  | 158  |
| EX-SUS-SFT STD | EA829SE-125 | 420  | 10 | 3  | 164  |
| EX-SUS-SFT STD | EA829SE-130 | 435  | 10 | 3  | 170  |
| EX-SUS-SFT STD | EA829SE-135 | 450  | 10 | 3  | 176  |
| EX-SUS-SFT STD | EA829SE-140 | 465  | 10 | 3  | 182  |
| EX-SUS-SFT STD | EA829SE-145 | 480  | 10 | 3  | 188  |
| EX-SUS-SFT STD | EA829SE-150 | 495  | 10 | 3  | 194  |
| EX-SUS-SFT STD | EA829SE-155 | 510  | 10 | 3  | 200  |
| EX-SUS-SFT STD | EA829SE-160 | 525  | 10 | 3  | 206  |
| EX-SUS-SFT STD | EA829SE-165 | 540  | 10 | 3  | 212  |
| EX-SUS-SFT STD | EA829SE-170 | 555  | 10 | 3  | 218  |
| EX-SUS-SFT STD | EA829SE-175 | 570  | 10 | 3  | 224  |
| EX-SUS-SFT STD | EA829SE-180 | 585  | 10 | 3  | 230  |
| EX-SUS-SFT STD | EA829SE-185 | 600  | 10 | 3  | 236  |
| EX-SUS-SFT STD | EA829SE-190 | 615  | 10 | 3  | 242  |
| EX-SUS-SFT STD | EA829SE-195 | 630  | 10 | 3  | 248  |
| EX-SUS-SFT STD | EA829SE-200 | 645  | 10 | 3  | 254  |
| EX-SUS-SFT STD | EA829SE-205 | 660  | 10 | 3  | 260  |
| EX-SUS-SFT STD | EA829SE-210 | 675  | 10 | 3  | 266  |
| EX-SUS-SFT STD | EA829SE-215 | 690  | 10 | 3  | 272  |
| EX-SUS-SFT STD | EA829SE-220 | 705  | 10 | 3  | 278  |
| EX-SUS-SFT STD | EA829SE-225 | 720  | 10 | 3  | 284  |
| EX-SUS-SFT STD | EA829SE-230 | 735  | 10 | 3  | 290  |
| EX-SUS-SFT STD | EA829SE-235 | 750  | 10 | 3  | 296  |
| EX-SUS-SFT STD | EA829SE-240 | 765  | 10 | 3  | 302  |
| EX-SUS-SFT STD | EA829SE-245 | 780  | 10 | 3  | 308  |
| EX-SUS-SFT STD | EA829SE-250 | 795  | 10 | 3  | 314  |
| EX-SUS-SFT STD | EA829SE-255 | 810  | 10 | 3  | 320  |
| EX-SUS-SFT STD | EA829SE-260 | 825  | 10 | 3  | 326  |
| EX-SUS-SFT STD | EA829SE-265 | 840  | 10 | 3  | 332  |
| EX-SUS-SFT STD | EA829SE-270 | 855  | 10 | 3  | 338  |
| EX-SUS-SFT STD | EA829SE-275 | 870  | 10 | 3  | 344  |
| EX-SUS-SFT STD | EA829SE-280 | 885  | 10 | 3  | 350  |
| EX-SUS-SFT STD | EA829SE-285 | 900  | 10 | 3  | 356  |
| EX-SUS-SFT STD | EA829SE-290 | 915  | 10 | 3  | 362  |
| EX-SUS-SFT STD | EA829SE-295 | 930  | 10 | 3  | 368  |
| EX-SUS-SFT STD | EA829SE-300 | 945  | 10 | 3  | 374  |
| EX-SUS-SFT STD | EA829SE-305 | 960  | 10 | 3  | 380  |
| EX-SUS-SFT STD | EA829SE-310 | 975  | 10 | 3  | 386  |
| EX-SUS-SFT STD | EA829SE-315 | 990  | 10 | 3  | 392  |
| EX-SUS-SFT STD | EA829SE-320 | 1005 | 10 | 3  | 398  |
| EX-SUS-SFT STD | EA829SE-325 | 1020 | 10 | 3  | 404  |
| EX-SUS-SFT STD | EA829SE-330 | 1035 | 10 | 3  | 410  |
| EX-SUS-SFT STD | EA829SE-335 | 1050 | 10 | 3  | 416  |
| EX-SUS-SFT STD | EA829SE-340 | 1065 | 10 | 3  | 422  |
| EX-SUS-SFT STD | EA829SE-345 | 1080 | 10 | 3  | 428  |
| EX-SUS-SFT STD | EA829SE-350 | 1095 | 10 | 3  | 434  |
| EX-SUS-SFT STD | EA829SE-355 | 1110 | 10 | 3  | 440  |
| EX-SUS-SFT STD | EA829SE-360 | 1125 | 10 | 3  | 446  |
| EX-SUS-SFT STD | EA829SE-365 | 1140 | 10 | 3  | 452  |
| EX-SUS-SFT STD | EA829SE-370 | 1155 | 10 | 3  | 458  |
| EX-SUS-SFT STD | EA829SE-375 | 1170 | 10 | 3  | 464  |
| EX-SUS-SFT STD | EA829SE-380 | 1185 | 10 | 3  | 470  |
| EX-SUS-SFT STD | EA829SE-385 | 1200 | 10 | 3  | 476  |
| EX-SUS-SFT STD | EA829SE-390 | 1215 | 10 | 3  | 482  |
| EX-SUS-SFT STD | EA829SE-395 | 1230 | 10 | 3  | 488  |
| EX-SUS-SFT STD | EA829SE-400 | 1245 | 10 | 3  | 494  |
| EX-SUS-SFT STD | EA829SE-405 | 1260 | 10 | 3  | 500  |
| EX-SUS-SFT STD | EA829SE-410 | 1275 | 10 | 3  | 506  |
| EX-SUS-SFT STD | EA829SE-415 | 1290 | 10 | 3  | 512  |
| EX-SUS-SFT STD | EA829SE-420 | 1305 | 10 | 3  | 518  |
| EX-SUS-SFT STD | EA829SE-425 | 1320 | 10 | 3  | 524  |
| EX-SUS-SFT STD | EA829SE-430 | 1335 | 10 | 3  | 530  |
| EX-SUS-SFT STD | EA829SE-435 | 1350 | 10 | 3  | 536  |
| EX-SUS-SFT STD | EA829SE-440 | 1365 | 10 | 3  | 542  |
| EX-SUS-SFT STD | EA829SE-445 | 1380 | 10 | 3  | 548  |
| EX-SUS-SFT STD | EA829SE-450 | 1395 | 10 | 3  | 554  |
| EX-SUS-SFT STD | EA829SE-455 | 1410 | 10 | 3  | 560  |
| EX-SUS-SFT STD | EA829SE-460 | 1425 | 10 | 3  | 566  |
| EX-SUS-SFT STD | EA829SE-465 | 1440 | 10 | 3  | 572  |
| EX-SUS-SFT STD | EA829SE-470 | 1455 | 10 | 3  | 578  |
| EX-SUS-SFT STD | EA829SE-475 | 1470 | 10 | 3  | 584  |
| EX-SUS-SFT STD | EA829SE-480 | 1485 | 10 | 3  | 590  |
| EX-SUS-SFT STD | EA829SE-485 | 1500 | 10 | 3  | 596  |
| EX-SUS-SFT STD | EA829SE-490 | 1515 | 10 | 3  | 602  |
| EX-SUS-SFT STD | EA829SE-495 | 1530 | 10 | 3  | 608  |
| EX-SUS-SFT STD | EA829SE-500 | 1545 | 10 | 3  | 614  |
| EX-SUS-SFT STD | EA829SE-505 | 1560 | 10 | 3  | 620  |
| EX-SUS-SFT STD | EA829SE-510 | 1575 | 10 | 3  | 626  |
| EX-SUS-SFT STD | EA829SE-515 | 1590 | 10 | 3  | 632  |
| EX-SUS-SFT STD | EA829SE-520 | 1605 | 10 | 3  | 638  |
| EX-SUS-SFT STD | EA829SE-525 | 1620 | 10 | 3  | 644  |
| EX-SUS-SFT STD | EA829SE-530 | 1635 | 10 | 3  | 650  |
| EX-SUS-SFT STD | EA829SE-535 | 1650 | 10 | 3  | 656  |
| EX-SUS-SFT STD | EA829SE-540 | 1665 | 10 | 3  | 662  |
| EX-SUS-SFT STD | EA829SE-545 | 1680 | 10 | 3  | 668  |
| EX-SUS-SFT STD | EA829SE-550 | 1695 | 10 | 3  | 674  |
| EX-SUS-SFT STD | EA829SE-555 | 1710 | 10 | 3  | 680  |
| EX-SUS-SFT STD | EA829SE-560 | 1725 | 10 | 3  | 686  |
| EX-SUS-SFT STD | EA829SE-565 | 1740 | 10 | 3  | 692  |
| EX-SUS-SFT STD | EA829SE-570 | 1755 | 10 | 3  | 698  |
| EX-SUS-SFT STD | EA829SE-575 | 1770 | 10 | 3  | 704  |
| EX-SUS-SFT STD | EA829SE-580 | 1785 | 10 | 3  | 710  |
| EX-SUS-SFT STD | EA829SE-585 | 1800 | 10 | 3  | 716  |
| EX-SUS-SFT STD | EA829SE-590 | 1815 | 10 | 3  | 722  |
| EX-SUS-SFT STD | EA829SE-595 | 1830 | 10 | 3  | 728  |
| EX-SUS-SFT STD | EA829SE-600 | 1845 | 10 | 3  | 734  |
| EX-SUS-SFT STD | EA829SE-605 | 1860 | 10 | 3  | 740  |
| EX-SUS-SFT STD | EA829SE-610 | 1875 | 10 | 3  | 746  |
| EX-SUS-SFT STD | EA829SE-615 | 1890 | 10 | 3  | 752  |
| EX-SUS-SFT STD | EA829SE-620 | 1905 | 10 | 3  | 758  |
| EX-SUS-SFT STD | EA829SE-625 | 1920 | 10 | 3  | 764  |
| EX-SUS-SFT STD | EA829SE-630 | 1935 | 10 | 3  | 770  |
| EX-SUS-SFT STD | EA829SE-635 | 1950 | 10 | 3  | 776  |
| EX-SUS-SFT STD | EA829SE-640 | 1965 | 10 | 3  | 782  |
| EX-SUS-SFT STD | EA829SE-645 | 1980 | 10 | 3  | 788  |
| EX-SUS-SFT STD | EA829SE-650 | 1995 | 10 | 3  | 794  |
| EX-SUS-SFT STD | EA829SE-655 | 2010 | 10 | 3  | 800  |
| EX-SUS-SFT STD | EA829SE-660 | 2025 | 10 | 3  | 806  |
| EX-SUS-SFT STD | EA829SE-665 | 2040 | 10 | 3  | 812  |
| EX-SUS-SFT STD | EA829SE-670 | 2055 | 10 | 3  | 818  |
| EX-SUS-SFT STD | EA829SE-675 | 2070 | 10 | 3  | 824  |
| EX-SUS-SFT STD | EA829SE-680 | 2085 | 10 | 3  | 830  |
| EX-SUS-SFT STD | EA829SE-685 | 2100 | 10 | 3  | 836  |
| EX-SUS-SFT STD | EA829SE-690 | 2115 | 10 | 3  | 842  |
| EX-SUS-SFT STD | EA829SE-695 | 2130 | 10 | 3  | 848  |
| EX-SUS-SFT STD | EA829SE-700 | 2145 | 10 | 3  | 854  |
| EX-SUS-SFT STD | EA829SE-705 | 2160 | 10 | 3  | 860  |
| EX-SUS-SFT STD | EA829SE-710 | 2175 | 10 | 3  | 866  |
| EX-SUS-SFT STD | EA829SE-715 | 2190 | 10 | 3  | 872  |
| EX-SUS-SFT STD | EA829SE-720 | 2205 | 10 | 3  | 878  |
| EX-SUS-SFT STD | EA829SE-725 | 2220 | 10 | 3  | 884  |
| EX-SUS-SFT STD | EA829SE-730 | 2235 | 10 | 3  | 890  |
| EX-SUS-SFT STD | EA829SE-735 | 2250 | 10 | 3  | 896  |
| EX-SUS-SFT STD | EA829SE-740 | 2265 | 10 | 3  | 902  |
| EX-SUS-SFT STD | EA829SE-745 | 2280 | 10 | 3  | 908  |
| EX-SUS-SFT STD | EA829SE-750 | 2295 | 10 | 3  | 914  |
| EX-SUS-SFT STD | EA829SE-755 | 2310 | 10 | 3  | 920  |
| EX-SUS-SFT STD | EA829SE-760 | 2325 | 10 | 3  | 926  |
| EX-SUS-SFT STD | EA829SE-765 | 2340 | 10 | 3  | 932  |
| EX-SUS-SFT STD | EA829SE-770 | 2355 | 10 | 3  | 938  |
| EX-SUS-SFT STD | EA829SE-775 | 2370 | 10 | 3  | 944  |
| EX-SUS-SFT STD | EA829SE-780 | 2385 | 10 | 3  | 950  |
| EX-SUS-SFT STD | EA829SE-785 | 2400 | 10 | 3  | 956  |
| EX-SUS-SFT STD | EA829SE-790 | 2415 | 10 | 3  | 962  |
| EX-SUS-SFT STD | EA829SE-795 | 2430 | 10 | 3  | 968  |
| EX-SUS-SFT STD | EA829SE-800 | 2445 | 10 | 3  | 974  |
| EX-SUS-SFT STD | EA829SE-805 | 2460 | 10 | 3  | 980  |
| EX-SUS-SFT STD | EA829SE-810 | 2475 | 10 | 3  | 986  |
| EX-SUS-SFT STD | EA829SE-815 | 2490 | 10 | 3  | 992  |
| EX-SUS-SFT STD | EA829SE-820 | 2505 | 10 | 3  | 998  |
| EX-SUS-SFT STD | EA829SE-825 | 2520 | 10 | 3  | 1004 |
| EX-SUS-SFT STD | EA829SE-830 | 2535 | 10 | 3  | 1010 |
| EX-SUS-SFT STD | EA829SE-835 | 2550 | 10 | 3  | 1016 |
| EX-SUS-SFT STD | EA829SE-840 | 2565 | 10 | 3  | 1022 |
| EX-SUS-SFT STD | EA829SE-845 | 2580 | 10 | 3  | 1028 |
| EX-SUS-SFT STD | EA829SE-850 | 2595 | 10 | 3  | 1034 |
| EX-SUS-SFT STD | EA829SE-855 | 2610 | 10 | 3  | 1040 |
| EX-SUS-SFT STD | EA829SE-860 | 2625 | 10 | 3  | 1046 |
| EX-SUS-SFT STD | EA829SE-865 | 2640 | 10 | 3  | 1052 |
| EX-SUS-SFT STD | EA829SE-870 | 2655 | 10 | 3  | 1058 |
| EX-SUS-SFT STD | EA829SE-875 | 2670 | 10 | 3  | 1064 |
| EX-SUS-SFT STD | EA829SE-880 | 2685 | 10 | 3  | 1070 |
| EX-SUS-SFT STD | EA829SE-885 | 2700 | 10 | 3  | 1076 |
| EX-SUS-SFT STD | EA829SE-890 | 2715 | 10 | 3  | 1082 |
| EX-SUS-SFT STD | EA829SE-895 | 2730 | 10 | 3  | 1088 |
| EX-SUS-SFT STD | EA829SE-900 | 2745 | 10 | 3  | 1094 |
| EX-SUS-SFT STD | EA829SE-905 | 2760 | 10 | 3  | 1100 |
| EX-SUS-SFT STD | EA829SE-910 | 2775 | 10 | 3  | 1106 |
| EX-SUS-SFT STD | EA829SE-915 | 2790 | 10 | 3  | 1112 |
| EX-SUS-SFT STD | EA829SE-920 | 2805 | 10 | 3  | 1118 |
| EX-SUS-SFT STD | EA829SE-925 | 2820 | 10 | 3  | 1124 |
| EX-SUS-SFT STD | EA829SE-930 | 2835 | 10 | 3  | 1130 |
| EX-SUS-SFT STD | EA829SE-935 | 2850 | 10 | 3  | 1136 |
| EX-SUS-SFT STD | EA829SE-940 | 2865 | 10 | 3  | 1142 |
| EX-SUS-SFT STD | EA829SE-945 | 2880 | 10 | 3  | 1148 |
| EX-SUS-SFT STD | EA829SE-950 | 2895 | 10 | 3  | 1154 |
| EX-SUS-SFT STD | EA829SE-955 | 2910 | 10 | 3  | 1160 |
| EX-SUS-SFT STD | EA829SE-960 | 2925 | 10 | 3  | 1166 |
| EX-SUS-SFT STD | EA829SE-965 | 2940 | 10 | 3  | 1172 |
| EX-SUS-SFT STD | EA829SE-970 | 2955 | 10 | 3  | 1178 |
| EX-SUS-SFT STD | EA829SE-975 | 2970 | 10 | 3  | 1184 |
| EX-SUS-SFT STD | EA829SE-980 | 2985 | 10 | 3  | 1190 |
| EX-SUS-SFT STD | EA829SE-985 | 3000 | 10 | 3  | 1196 |
| EX-SUS-SFT STD | EA829SE-990 | 3015 | 10 | 3  | 1202 |
| EX-SUS-SFT STD |             |      |    |    |      |